









Enabling Devices Communicator Feature Comparison






Non-Voice Devices







DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Go! Boards 6 or 8 Icons #3336 & #3338		6 or 8 — 2" x 2"	6 or 8	N/A	N/A	N/A	\$51.95- \$55.95	Designed for those who would benefit from a picture schedule. Pictures or symbols representing a desired activity or task can be framed in the icon holders. When the activity is completed, the icon holder is removed and placed into the pocket at the base. Size: 23" x 5½" x 3". Size: 29" x 5½" x 3".
Go! Boards 21 Icons #3349 & #3348		21 — 2" x 2" or 3" x 3"	21	N/A	N/A	N/A	\$72.95- \$89.95	Board allows user to make choices at each time period in their schedule. They can choose one of 3 activities in any one of the 7 scheduled time slots. Size: 26½"L x 11"W x 3"H. Size: 34"L x 15"W x 4"H.
Clock Communicators #1200		N/A	4 to 8	N/A	Switch	N/A	\$135.95	Helps communicate thoughts, switch activation moves the clock hand to the desired picture or word affixed to the clockface. You can customize the communication by using as few or as many objects as you'd like. Size: 16½"L x 14½"W x 5"H. Requires 1 9-V Battery.
Compartmental Clock Communicators #1231		8 — ¾" and 1¼" deep	8	N/A	Switch	N/A	\$126.95	Ideal for users with impaired vision. Has eight compartments to hold items. When the external capability switch is activated, the clock hand moves to the desired picture, word or object affixed to the clockface. When 2 switches are being used, one turns the clockhand clockwise while the other will bring it counter-clockwise. Size: 17"L x 16"W x 6"H. Requires 1 9-V Battery.



DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Eye Talks #3700		N/A 17" x 11½" x 1/16"	N/A	N/A	N/A	N/A	\$17.95	Helps make eye-gaze communication more accurate and understandable! We have constructed a very affordable communication device that opens up a whole new world of social communication skills. The Eye-Talk is a great alternative for children and adults who need to communicate. It is made with clear, shatter-resistant plastic. Size: 17" x 11½" x 1/16".

Single Message Devices



DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Big Talk #4200		1 5¼"	1	20	Direct or Switch	Input Switch & Device Output	\$93.95	Single message output with a large (5 1/4") activation surface. Device also acts as a switch so you can activate another device of your choice. Comes in five colors. Size: 7" x 4½". Requires 4 AA Batteries.
Small Talk #4201R, Y, B, G & P		1 2½"	1	20	Direct or Switch	Input Switch & Device Output	\$84.95	The user can play recorded messages with the slightest touch on the small (2½") activation surface. A special holder allows you to show an icon, word or photo. Device also acts as a switch so you can activate a device when the message is playing. The Small Talk can also be activated by an external switch. Size: 2½"L x 5½"W x 5½"D. Requires 4 AAA Batteries.
Mini-Com #9151		1 4" x 3 3/8"	1	20	Direct	N/A	\$69.95	Use these communicators individually or join them for building communication skills. Easy to use picture clip allows you to change icons easily. Size: 5½"L x 6"W x 3"H. Requires 4 AA Batteries.






DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Wrist Talker #3037 & #3037B		1 1"	1	10	Direct	N/A	\$42.95	The slightest push on the face of this wrist communicator will provide a recorded message. Great sound quality will enable the user to communicate any greeting. Has an adjustable strap and is available in blue or black. Size: 2¼" x 1½". Requires 4 LR44 Button Cells (Included).
Talking Picture Card Holder #9150		1 5" x 2"	1	20	Direct	N/A	\$92.95	The vertical placement of pictures encourages the user to maintain his/her head in an upright position. The picture cards are held behind a clear durable cover and can be easily changed. As new skills are acquired, these communicators can be connected together with their Velcro attachments. Size: 7" x 7½" x 8½". Requires 4 AA Batteries.
Talking Alert #1412 & w/12-Levels #1412-L		1 5¼"	1 & 12	20 or 288	Direct	N/A	\$114.95- \$126.95	Pressing the textured lens turns on a bright light and starts your message. While the message is playing, a circle of lights indicate that words are being played. The 12-level unit allows you to record and play twelve 24-second messages. A special switch on the side of the unit selects levels. Size: 7¼"W x 2½"H. Requires 4 AA Batteries.
Put-Em-Arounds #9012		1 5¼" x 3¾"	1	20	Direct	N/A	\$66.95	These talking wall communicators give non-verbal children the ability to initiate communication throughout their day. Have the children actively participate with their peers, family, and teachers. Put them in different areas of your classroom or house to express simple messages. Recording and re-recording requires only the push of a button. Size 6½"W x 8"L. Requires 4 AA Batteries.
Happy Time #8015		1 3" x 3"	1	20	Direct	N/A	\$74.95	This delightful Put-Em-Around expresses your pre-recorded message when activating the icon frame. During the time the message is played, lights stay on showing the hearing impaired user that a message is being communicated. Size: 9"L x 5¼"W x 2½"H. Requires 4 AA Batteries.

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
One Take or Place N' Talk #8708		1 — 5¼" x 5½"	1	20	Direct	N/A	\$79.95	Our popular Take N' Talk is now available as a single unit for focusing on a specific task. Removing or placing the object of your choice will play your pre-recorded message. Icons can be placed under a clear removable panel. Size: 11¼"L x 2¼"W x 7½"H. Requires 4 AA Batteries.
Motion Talker #1519		N/A — N/A	1	20	N/A	N/A	\$44.95	The slightest movement in front of the seeing-eye sensor causes your recording to play. Can be used to elicit movements in even the most involved individuals. You can reward gait training, wheelchair control, gross and fine motor movements, as well as a variety of other therapeutic objectives. Size: 3¼" x 3" x 4½". Requires 4 AA Batteries.
Side Swiping #9152		N/A — N/A	1	20	Direct	N/A	\$86.95	For those clients who require a "side swiping" communication device we have integrated our Wobble Switch. It has a ledge for holding icons. Size: 11"L x 7"W x 5"H. Requires 4 AA Batteries.
Koosh Say It Play It #881		N/A — N/A	1	20	Direct	Device Output	\$89.95	This device will play your messages while simultaneously activating any connected device. Contains latex. Size: 8" x 6" x 4". Requires 4 AA Batteries.
Saucer Dome Say It Play It #9158		N/A — 6" x 3¼"	1	20	Direct	Device Output	\$103.95	Pressing the dome will reward the user with vibration and your pre-recorded message. It is easy to record and re-record any songs or words by pressing a hidden switch. A cord is provided which simultaneously activates an external device. Size: 8"W x 4½"H. Requires 6 AA Batteries.
Say It Play It Switch Plate #1313		1 — 5" x 8"	1	20	Direct	Device Output	\$85.95	Our exclusive Say It Play It switch is great for promoting cause and effect. Connect an adapted toy or device to the large switch plate. When the plate is touched, it will simultaneously activate the message and any connected toy or device. Size: 10¼" x 7¼" x 3". Requires 4 AA Batteries.





DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Single Message Devices #1414		1 5" x 2"	1	20	Direct	N/A	\$65.95	Insert your photograph, icon or message in the holder. Size: 5"L x 6"W x 1½"H. Requires 4 AA Batteries.
Prop Holder Communicator #9081		1 5¾" x 4¼"	1 or 7	30-210	Direct or Switch	N/A	\$200.95	Attach any picture to the stick then activate the attached yellow switch plate and watch the picture swing side to side while your recorded message plays. Record messages of up to 30 seconds on 7 levels for a total of 210 seconds of recording time. A built-in electronic circuit allows the user to select latched, timed, or momentary output. Size: 7"H x 9"D x 6½"W. Requires 4 AA Batteries.

Two Message Devices







DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Talkable II #2400		2 2½"	2	20	Direct	2 Device Outputs	\$109.95	This compact message communicator allows for simple communication and come with built-in icon holders. Choose between two activities such as asking and answering questions (e.g. yes, no). It has output jacks to simultaneously activate two devices. Size: 7½"L x 4½"W x 3"H. Requires 4 AAA Batteries.
Twin Talks #1405 & #1406		2 3" x 5"	2	20	Direct	#1406 has a device output	105.95- \$136.95	Twin Talk is the ideal trainer, teacher and communicator. Use it to request attention, communicate needs, make simple choices, sing a song, make sound effects, participate in games, and more. Available in two helpful models: Twin Talk (speaks only) and Twin Talk and Play (simultaneously "speaks" and activates a toy or device). Size: 13" x 6½" x 2". Requires 4 AA Batteries.






DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Rocking Plates #1398 Rocking Say It Play It #1399		2 — 12" x 3¼"	2	20	Direct	N/A 2 Device Outputs	96.95- \$102.95	The Rocking Plate allows you to play two 10-second messages. For example, you could record yes/no responses to questions or any other desired messages. Size: 14"L x 6"W x 2½"H. Requires 4 AA Batteries. Great for developing correlation between language and function. Our Say It Play It simultaneously activates two toys or devices using the cords (included) and plays back two messages. Size: 14"L x 6"W x 2½"H. Requires 4 AA Batteries.
Two Compartments Communicator #1243		2 — 2½" x 4¼"	2	20	Direct	N/A	\$124.95	Our exclusive compartmentalized communicator is fun, easy to use, and perfect for teaching language skills (classification, sequence, function, opposites and comparatives). Place objects, pictures or words in each of the compartments. Activating the switch plate plays the message while turning on one light at a time. Size: 1" x 10½" x 3". Requires 4 AA Batteries.
Rocking Two Message with Light #1409		2 — 2" x 2"	2	20	Direct	N/A	\$124.95	Light goes on when message is played. Frames allow you to insert a picture or message. Size: 5"L x 6"W x 1½"H. Requires 4 AA Batteries.
Hip Talk #5002		2 — 2" x 2½"	2	20	Direct	N/A	\$104.95	Perfect for kids and adults alike, our unique Hip Talk communicator plays messages at the push of a button. Comes in a soft, nylon zippered pack with a waist strap. Size: 6¼" x 2¼" x 3¼". Requires 4 AA Batteries.
Clip Talk #5529		N/A — N/A	1 or 2	20	Direct or Switch	N/A	\$79.95	Our portable Clip Talk communicator allows you to record and re-record one 20-second or two 10-second messages. It contains a spring reinforced clip that snaps onto a wheelchair, walker, bedrail, stroller or virtually any other tubular or rectangular object. Size: 6½" x 4" x 5¼". Requires 4 AA Batteries.






Three Message Devices




DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Talkable III #2401		3 — 2½"	3	15	Direct	3 Device Outputs	\$119.95	The Talkable III allows for three 5-second messages. Three jacks allow you to simultaneously activate a toy or device for immediate reinforcement. Size: 7½"L x 4½"W x 3"H. Requires 4 AAA Batteries.
Grooved Platform #1900 & #1910		3 — 4" x 4¾"	3	15	Direct	N/A	\$126.95- \$163.95	This colorful, creative tool is ideal for teaching communication skills and object/word relationships. Place objects, words or pictures on the raised platform, press the appropriate switchplate and lights and a 5-second pre-recorded voice message will play. #1900 plays a soothing tone when the plate is pressed. #1901 plays three 5-second pre-recorded messages. Size: 16½" x 12" x 3½". Requires 4 AA Batteries.
Three Compartment Communicator #1253		3 — 2½" x 4¼"	3	20	Direct	N/A	\$159.95	Our exclusive compartmentalized communicator is fun, easy to use, and perfect for teaching language skills (classification, sequence, function, opposites and comparatives). Place objects, pictures or words in each of the compartments. Comes with space for your objects and holders for your photos. Activating the switch plate plays the message while turning on one light at a time. Size: 14" x 10½" x 3". Requires 4 AA Batteries.
Compact Communicator #1901		3 — 2" x 3"	3	15	Direct	N/A	\$92.95	Go-anywhere communicators that can be used with pictures or objects. Small enough to fit comfortably on a lap or wheelchair table. The top of these mini communicators are compartmentalized allowing you to place the objects that are described in your pre-recorded messages. Pictures can also be placed in a special holder. Light goes on when switch plate is pressed and the message plays. Size: 9"L x 6"W x 1½"H. Requires 4 AA Batteries.

Four Message Devices


DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Talkable IV #2402		4 — 2½"	4	20	Direct	4 Device Outputs	\$129.95	This compact message communicator allows for simple communication and comes with built-in icon holders. Size: 14"L x 5½"W x 2¾"H. Requires 4 AA Batteries.
Choice 4 #1237		4 — 2" x 2"	4 on 12 levels	300	Direct & Switch with Scanning	N/A	\$399.95	This unique communicator allows you to sequentially illuminate objects, photographs or icons with its super bright lights. The device also allows you to adjust the number of choices based upon the skills of the user. Work with just one field or add two, three or four fields. Size: 8"L x 15½"W x 3"H. Requires 4 D Batteries.
Language Facilitator #3057		4 — 2" x 2"	4	120	Direct	N/A	\$189.95	Pre-record your 4 message communicator with up to 30 seconds of time in each square. The user selects a message or sound to hear, and then she can watch herself pronounce the word or sounds in the 11" x 15" mirror while lights around the rim help her to visually attend. Size: 12"L x 12"W x 17"H. Requires 4 AA Batteries.
Cheap Talk 4 In-line #3054		4 — 2" x 2"	4	20	Direct	N/A	\$112.95	Activated by pressing one of the four squares. Size: 12½" x 3" x 6". Requires 4 AA Batteries.
Cheap Talk Square #1392		4 — 2" x 2"	4	20	Direct	N/A	\$107.95	Activated by pressing one of four squares. Size: 8" x 8" x 3". Requires 4 AA Batteries.
Hip Talk 4 Message #5004		4 — 1" x 2"	4	20	Direct	N/A	\$122.95	Perfect for kids and adults alike, our unique Hip Talk communicators play messages at the push of a button. Come in a soft, nylon zippered pack with a waist strap. Size: 6¼" x 2¼" x 3¼". Requires 4 AA Batteries.





DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Talk 4 w/Levels #2500 & #2500B		4 2 1/8" x 2 1/8"	4 on 12 levels	300	Direct & Switch w/Scanning	N/A	\$229.95	Our Talk 4 Augmentative Communicators are powerful communication tools loaded with useful features. Talk 4 has single switch illuminated auto scanning. It has a slot so you can easily slide in your icon overlay. Icon area requires only the slightest touch to play your "true voice" recording. The rugged and reliable Talk 4 is portable, lightweight and easy to access. Size: 11"L x 4"W x 2 3/4"H. Requires 4 AA Batteries.
Super Wrist Talker #5018		N/A	4 on 12 levels	20 to 240	Direct	N/A	\$169.95	Our new compact Super Wrist Talker enables the user to communicate any need or greeting with its color coded button system. Has adjustable straps and is comfortable to wear. Size: 4"L x 2 1/8"W x 1"H. Requires 2 AAA Batteries.
Take or Place N' Talk Series #8701P, 8702P, (8703P - 3" x 3"), 8704P & 8705		4 Varies	1 to 4	20	Direct	#8705 Only Input Switch	125.95- \$135.95	Each is a self-contained device which allows the user to record 1 to 4 different messages. You play the messages back by removing "taking" an item (of your choice) from one of the light sensitive compartments (TAKE mode) or "placing" the item in one of the compartments (PLACE mode). Requires 4 AA Batteries.
Upright Take N Talk #8709		4 2" x 2"	4	20	Direct	N/A	\$104.95	New design allows the Take or Place N' Talk to be secured to a table with clamps. Size: 13 1/4"L x 4"W x 3 1/2"H. Requires 4 AA Batteries.
Compact Communicators #1902 & 1903		4 2" x 3"	#1902 4 #1903 4 on 12 levels	#1902 20 sec #1903 288 sec	Direct	N/A	125.95- \$135.95	Go-anywhere communicators that can be used with pictures or objects. Small enough to fit comfortably on a lap or wheelchair table. The top of these mini communicators are compartmentalized allowing you to place the objects that are described in your pre-recorded messages. Pictures can also be placed in a special holder. Light goes on when switch plate is pressed and the message plays. Size: 11 1/2"L x 6 1/4"W x 1 1/2"H. Requires 4 AA Batteries.




DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Put-Em-Around #9014		N/A 3" x 3"	4	20	Direct	N/A	\$87.95	Great to put in your home, classroom or therapy areas. Pressing on each of the four corners of the front plate plays one of your four pre-recorded messages. Size: 7"L x 9"W x 1½"H. Requires 4 AA Batteries.
Four Compartment #1245 & #1246		4 2½" x 4¼"	#1245 4 #1246 4 on 12 levels	20 288	#1245 Direct #1246 Direct & Switch w/2 scan modes	Input Switch	\$189.95- \$209.95	Pushing the colored plate below the icon holder plays your pre-recorded message while the bright light shines. #1246 has Linear scanning. Choose either automatic or inverse scanning with your external switch. Size: 18"L x 10"W x 6"H. Requires 4 AA Batteries.
Super-Sized Communicator #1221		4 2¾" x 4¼"	4 on 12 levels	288	Direct or Switch w/2 scan modes	N/A	\$204.95	Each compartment has its own switch for direct selection. Linear scanning allows the user to scan objects, photographs or symbols by activating a capability switch. Now choose either automatic or inverse scanning. Adjustable scan rate, easy to use photograph holder and easy to change icons. Size: 28"L x 11½"W x 4¼"H. Requires 4 AA Batteries.
Compartmentalized Communicator #1239		4 2¾" x 4¼"	4	20	Direct	N/A	\$189.95	Our compartmentalized communicator is fun, easy to use, and perfect for teaching language skills (classification, sequence, function, opposites and comparatives). Place objects, pictures or words in each of the compartments. Activating the switch plate plays the message while turning on one light at a time. Size: 19" x 10" x 3". Requires 4 AA Batteries.
4-Plate Communicator Say It Play It #4055		4 3" x 5"	4	20	Direct	4 Device Outputs	\$119.95	This communicator provides a large target area for individuals who cannot easily access smaller communication devices. This versatile communicator can be positioned at a 30 degree angle or a 70 degree angle. The communicator also allows the user to simultaneously communicate and activate four different toys or devices. Size: 15"L x 7½"W x 7½"H. Requires 4 AA Batteries.


DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Talking Pin Say It Play It #9157		N/A — N/A	4	20	Direct	4 Device Outputs	\$112.95	By pushing the happy pin like a joystick, four separate messages can be played. Four switch output jacks are provided which can simultaneously activate four separate devices. Size: 8¼"W x 9"H x 7½"D. Requires 4 AA Batteries.
Palm Say It Play It #9121		N/A — 4"	4	20	Direct	4 Device Outputs	\$85.95	The slightest push in one of four directions will result in one of four pre-recorded messages playing with the option of devices being activated simultaneously. Size: 9"L x 4"W x 3½"H. Requires 4 AA Batteries.
Companion Communicator #3034		4 — ½"	4	20	Direct	N/A	\$99.95	Recording your messages is easily accomplished. The buttons are covered with a clear durable cap which allows you to mount and protect your icons. This unit is easily attached with its belt clip or held by a removable loop (included). Size: 3¼"L x 3"W x 1¼"H. Requires 4 AAA Batteries.

Sequencers



DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
NEW! Speak a Need #1254		2 — 3"	10 Needs messages & 10 Response messages per level — 5 levels	300	Direct	Input Switch	\$184.95	A great new auditory communicator for expressing your needs. Simple and fast to program and use. This versatile five level communicator allows the recording of five different categories of needs which could include food, bathing, and health needs. Once a category is chosen, pushing the red button sequences through a list of items (up to ten items) within that category. Size: 4"H x 8½"W x 4½"D. Requires 4 AAA Batteries.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
NEW! Announcer & Table Top Announcer w/6 Levels #5015 & #5021		1 3"	10 Messages per level including level announcement 6 levels	5 sec per message total 300	Direct or Switch	Input Switch	\$259.95- \$279.95	Our new sequencer communicator allows the user to first hear a series of words and then select one by simply activating its capability switch. Available on a 24" Gooseneck or tabletop. #5015 Size: 26"H x 6"W. Requires 4 AA Batteries. #5021 Size: 6½"L x 6¼"W x 3"H. Requires 4 AAA Batteries.
Big Talk Triple Play #4204R, Y, B, G & P		1 5¼"	Unlimited within total time 4 levels	75 sec per level total 300	Direct or Switch	Input Switch & Device Output	\$154.95	Single, sequential and random message capabilities with an output for activating other devices. Just push the round plate and your pre-recorded words can be played back in single, sequential or random order. Sequential capability is great for storytelling. Random capability is great for playing games that use dice, spinners, cards and more. Size: 7" x 4½". Requires 4 AA Batteries.
Small Talk Sequencer #8151		1 2½"	250	300	Direct or Switch	Input Switch & Device Output	\$96.95	Single, sequential, and random message capabilities with an output for activating other devices. Sequential capability is great for storytelling, singing songs, telling a joke or carrying on a conversation with your friends. Press the plate the first time and the first message is spoken; press it again and the second message is spoken; etc. Random capability is great for playing games that use dice, spinners, cards and more. Size: 6¼"L x 6¼"W x 3"H. Requires 4 AAA Batteries.
Mini-Com Sequencer #9151-S		1 4" x 3 3/8"	Unlimited w/in 300 seconds	300	Direct	N/A	\$104.95	We've added sequencing to our best-selling Mini-Com! Use this device individually or join it with our basic Mini-Coms for sequencing, storytelling, sing-along, telling a joke or carrying on a conversation. Press the plate the first time and the first message is spoken; press it again and the second message is heard; etc. Easy-to-use picture holder allows you to easily change photographs. Size: 5½"L x 6"W x 3"H. Requires 4 AA Batteries.




DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Hip Step-Talking Sequencer #5075		1 — 2" x 2½"	Unlimited w/in 300 seconds	300	Direct	N/A	\$105.95	Our exclusive Hip Step-Talking Sequencer is the perfect portable communicator for the non-speaking adult or child. Compact in size, it enables people with even the most limited communication skills to carry on the conversation which you have recorded for them. To use, just press the play-plate to play the messages sequentially. Great for sequencing, testing, instructions, multiplication, memorization, sing-alongs, storytelling and more. Size: 6¼" x 2¼" x 3¼". Requires 4 AA Batteries.
Adjustable Angle Sequencer #806		1 — 5"	Unlimited w/in 300 seconds	300	Direct	Device Output	\$170.95	Our new sequencer is designed for the visually impaired. The circular patterned red LED lights in the center give the user a visual cue for targeting and encourage the user to activate the switch. The angle of the big 5" switch is adjustable from 32 degrees to 90 degrees. The light can be turned on or off. Size: 8"L x 8"W x 6¼"H. Requires 4 AA Batteries.
Step Talking Sequencers #1355 #653 #1481 #673 #668		Varies — Varies	Unlimited w/in 300 seconds	300	Direct	N/A	\$117.95	Our Step Talking Sequencers are perfect for the non-speaking adult or child. It allows the user to express a sequential series of your pre-recorded messages. The sequencer allows people with even the most limited communication skills to carry on a simple conversation. Ideal for a number of different purposes including sequencing, testing, directions, multiplication, memorization, medical instructions, storytelling and sing-alongs. Now available in five different models. Size: 9¾" x 8¾" x 2½". Requires 4 AA Batteries.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Talking Magic Roller #1652		N/A N/A	Unlimited w/in 300 seconds	5 min	Direct & Switch	Input Switch for Base	\$189.95	The slightest touch rolls the cylinder and starts your story, songs or ABCs. This learning toy has a built-in sequential recorder which allows you to record and play. For example, roll and the first message is spoken; roll again and the second message is heard; etc. Simultaneously, the lights flash and the roller vibrates. Further, if the child cannot roll the unit, a capability switch (not included) can be used which runs on the built-in roller motor. The roller sequencer also can be removed from its stand and played with on a table or floor. Roller Size: 6"D x 6"H. Requires 4 AA Batteries. Base Size: 8½"L x 12"W x 5"H. Requires 2 AA Batteries.






Randomizers


DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Big Talk Triple Play #4204R, Y, B, G & P		1 5¼"	Unlimited w/in 300 seconds	300	Direct or Switch	Input Switch & Device Output	\$154.95	Single, sequential and random message capabilities with an output for activating other devices. Just push the round plate and your pre-recorded words can be played back in single, sequential or random order. Sequential capability is great for storytelling. Random capability is great for playing games that use dice, spinners, cards and more. One can play a message while activating your device. Size: 7" x 4½". Requires 4 AA Batteries.
Small Talk Sequencer #8151		1 2½"	Unlimited w/in 300 seconds	300	Direct or Switch	Input Switch & Device Output	\$96.95	Single, sequential, and random message capabilities with an output for activating other devices. Sequential capability is great for storytelling, singing songs, telling a joke or carrying on a conversation with your friends. Press the plate the first time and the first message is spoken; press it again and the second message is spoken; etc. Random capability is great for playing games that use dice, spinners, cards and more. Size: 6¼"L x 6¼"W x 3"H. Requires 4 AAA Batteries.

Five to Seven Message Devices



DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
7 Message Take or Place N' Talk Go! Board #3347		7 — 3" x 3"	7	245	Direct	N/A	\$181.95	Record seven messages then play the message back by removing or placing one of the 3" x 3" icon frames. Pocket on the front of the unit can be used for storage. Size: 29½" x 5¼" x 3". Requires 4 AA Batteries.
Carousel Communicator #429 & #426		7 — 2" x 2"	#429 has 7 — #426 has 7 on 6 levels	260	Direct	N/A	\$199.95- \$222.95	Carousel allows you to easily select messages. Seven icon holders (included) are attached to the unit with velcro so that they can be changed easily. Size: 13" x 4". Requires 4 AA Batteries.
7 Message Take or Place N' Talk Tabletop w/6-levels #3350-B		7 — 2" x 2"	7 on 6 levels	288	Direct	N/A	\$225.95	We have added a removable platform on the back of the communicator for object placement. The communicator's ergonomically designed shape makes it easy to use for those with limited range. Your message is played by removing or placing one of the 2" x 2" icons. When the level changer button is pushed, this communicator announces (your recording) the contents of each selected level, e.g. food, transportation, comfort, etc. Size: 20"L x 5¼"W x 3½"H. Requires 4 AA Batteries.
Advanced Auditory Communicator #4398		7 — 2" x 2"	7 on 6 levels	300	Direct	N/A	\$320.95	Our newest communicator has auditory cueing. Push any of the picture icons to hear your chosen message in a low volume; push the message again and it plays the chosen message in an amplified volume. Simply slide in the interchangeable picture icons to enhance expressive and receptive language. The bottom right switch is the level changer with a level announcing message. Device stores up to 48 six second messages including the level announcing recordings. Size: 12"W x 2¼"H x 8"D. Requires 4 AA Batteries.

Eight Message Devices




DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Cheap Talk 8 Switch Module #1411		N/A — N/A	8	300	Switch	8 Input Switches	\$137.95	This handy module is a self-contained recorder-talker which accept one to 8 switches. Size: 3½" x 6" x 2¼". Requires 4 AA Batteries.
Cheap Talk 8 #1391		8 — 2" x 2"	8	300	Direct	N/A	\$199.95	Activated by pressing one of the eight message squares. Available in several models. Size: 12½" x 8" x 3". Requires 4 AA Batteries.
4/8 Object Communicator #1407		N/A — N/A	8 on 6 levels	240	Switch with scanning	Input Switch	\$259.95	This communicator allows the user to place items in enclosed compartments. As it scans through each place, it illuminates the object with 6 super bright lights. It can scan either 4 or 8 compartments allowing the user to build skills. Scan speed and volume are selected by switches on the back of the unit. Size: 17" x 12". Compartments 3¼" x 3¼" x 2¼" deep. Requires 4 AA Batteries.
Cheap Talk 8 6-levels #2391		8 — 2" x 2"	8 on 6 levels	300	Direct	N/A	\$279.95	Our exclusive 6-Level Communicator is ideal for teaching language skills and communicating. Messages can be recorded and re-recorded as often as you wish. Available in several models. Size: 12½"L x 8"W x 3"H. Requires 4 AA Batteries.
Talk 8 w/levels #2501		8 — 2½" x 2½"	8 on 12 levels	600	Direct & Switches w/scanning	Input Switch	\$359.95	Our Talk 8 has direct access and two Switch scanning, Automatic scanning, Inverse scanning, and Step scanning. Requires only the slightest touch to play your "true voice" recording. The rugged and reliable Talk 8 is portable, lightweight and easy to access. Size: 11½"L x 6½"W x 3"H. Requires 4 AA Batteries.

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Cheap Talk 8 Gooseneck #1338G		8 — 2 1/8" x 2 1/8"	8 on 6 levels	300	Direct	N/A	\$324.95	Our popular communicator is now available on a gooseneck. Great for those who cannot access tabletop communicators or who otherwise require special positioning. As with all of our Cheap Talks, it provides bright icon holders and easy to record messages. Size: 13 1/2"L x 8 1/2"W x 3 1/2"H. Requires 4 AA Batteries.


Nine to Fifteen Message Devices





DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Spinning Communicator #2043		12 — 2" x 2"	12	216	Direct	N/A	\$158.95	This easy access device works well for users who cannot access other communicators. It can be used in the classroom to match objects with words or pictures. With this storage capacity one might have songs or nursery rhymes recorded in the carousel. Icons can be changed with the turn of a screw. Size: 12" Diameter. Icon Opening: 2 1/4" x 2" x 1 1/2". Requires 4 AAA Batteries.
Hip Talk 12 w/levels #5013		12 — 7/8"	60	300	Direct & Auditory Cueing	N/A	\$269.95	Our bestselling Hip Talk 12 has major improvements: <ul style="list-style-type: none"> •5 levels with easy level changer •300 seconds of recording time •Incredible sound quality •Magnetic snap-on frame allows easy icon changing •New water resistant Neoprene carrying bag •Contoured for the waist •Adjustable waist strap to fit most •Sleep mode to save battery life •Volume control •Auditory cueing •On/Off switch. Size: 8 1/2"L x 3"W x 3 1/2"H. Requires 4 AAA Batteries.



Sixteen to Sixty-Four Message Devices

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Talking Photo Album #9127		24 4" x 6"	24	240	Direct	N/A	\$51.95	Create a 24-page talking communication book with photographs, icons and drawings. Press the bottom of the page to start your message. (Requires a moderate amount of pressure.) Great to use as an interactive storyteller, choice maker or slide show. Size: 5½"L x 7¾"W x 1¼"H. Requires 2 AAA Batteries.
32-Message Communicator #3206		32 2" x 2"	32 on 6 levels	576	Direct	N/A	\$296.95	Frame allows for easy changing of overlays. Lightweight, portable and built to last, this communicator has adjustable legs for tilting the unit, is shock resistant and has its own carrying handle. Size: 16"L x 9"W x 3"H. Requires 4 AA Batteries.
Phrase Maker Communicator #2509		15 1¼" x 1½"	15 on 7 levels	280	Direct & 3 additional access modes	N/A	\$435.95	Open up a world of communication choices with our new innovative Phrase Maker. The device allows the user to combine up to 15 of your pre-recorded words or short phrases to create their own unique sentences. The has FOUR modes: Direct Select with Auditory Queing, Single Switch Message Entry, Direct Select Beep Acknowledgement, and Direct Select. Size: 12¼"L x 10¼"W x 3¾"H. Requires 4 AA Batteries.



Progressive Communicators






DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Hip Talk Plus #5020		3, 6, 12 Varies (see website)	3, 6 or 12	300	Direct	Input Switch	\$249.95	The ultimate and newly improved Hip Talk Plus has major changes: •Incredible sound quality •Auditory cueing •Magnetic snap-on frames for easy icon changing •New waterproof Neoprene carrying bag •Contoured for the waist •Adjustable waist strap to fit most •Sleep mode to save battery life •Volume control •Low battery warning •3 interchangeable frames. Size: 8½"L x 3"W x 3½"H. Requires 4 AAA Batteries.

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Speak & Learn #767		2, 4, 8 & 16 — Varies (see website)	2, 4, 8 or 16 on 7 levels	300	Direct	N/A	\$184.95	Have fun individualizing this matching memory game. Pre-record your questions and answers and you're ready to play. This is an exciting way to reinforce identification and matching numbers, letters, shapes, and words. The tasks are endless. The grids are interchangeable with 2, 4, 8, and 16 windows. The included starter kit has six overlays (see above). Size: 14¼"L x 12½"W x 6½"W. Requires 4 AA Batteries.
Comm Builder #7071 & #7071B		1 to 16 — Varies (see website)	1 to 16	18 to 300	Direct	N/A	\$224.95	This Communication Builder is equipped with 5 easy to change frames, which allow you to refine communication choices as the person develops new skills. Record your own messages with the simplest push of a button. Light, durable and easy to carry with a built in handle. Frames included are 1, 2, 4, 8 and 16-window options. Re-recording is required when you change window frames. Frame size is 8½" x 7". Size: 12½"L x 9¼"W x 4"H. Requires 4 AA Batteries.
Scene Communicator #7074		1 to 16 — Varies (see website)	1 to 16 on 7 levels	300	Direct	N/A	\$395.95	Our unique language-enhancing communicator comes with seven colorful scene overlays which allow the user to communicate about his/her environment. Scenes include Playground, Classroom, Apartment, Pet Shop, Therapy Room, Birthday Party, and Grocery Store. This new portable communicator also comes with 5 clear plastic snap-in grid frames which allow the user to gradually select more detailed sections of the scenes. Size: 14¾"W x 6½"H x 12½"D. Requires 4 AA Batteries.
7-Level Communication Builder #7075 & #7075B On-the-Go 7-Level Communicator Builder #7075G		1 to 16 — Varies (see website)	1 to 16 on 7 levels	300	Direct	N/A	\$325.95	These Communication Builders allow the user to record and play back 1, 2, 4, 8, or 16 different messages per level. Re-recording is required when you change window frames. Time per level by window setting, using all seven levels. Frame size is 8½" x 7". Size: 12½"L x 9¼"W x 4"H. Requires 4 AA Batteries.


DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
4-Level Communication Builder #7077		1 to 16 Varies (see website)	1 to 16 on 7 levels	300	Direct	N/A	\$305.95	This Communication Builder is equipped with 5 easy to change frames, which allow you to refine communication choices as the person develops new skills. Additionally, a new feature allows this communicator to retain your recordings on all four levels when switching back and forth between window frames. Frame size is 8½" x 7". Size: 12½"L x 9¼"W x 4"H. Requires 4 AA Batteries.
Laptop Communicator - 7 Levels #7076		1 to 16 Varies	1 to 16 on 7 levels	300	Direct	N/A	\$305.95	This Communicator is a self-contained communication device, which allows the user to record and play back 1, 2, 4, 8 or 16 different messages per level. Re-recording is required when you change window frames. Frame size is 8½" x 7". Device size is 9½"L x 7½"W x 2¼"H. Requires 4 AA Batteries.

Devices for the Visually Impaired

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
NEW! Portable Communicator for the Visually Impaired #7079		8 3"	2 to 8 on 12 levels	600	Direct, Switch & Auditory Cueing	2 Input Switches	\$429.95	Designed for the visually impaired user, this unique state-of-the-art communicator provides intense background illumination of transparent icons. It is also extremely flexible – four scan modes and your choice of the number of fields to use. Size: 15"L x 9½"W x 2½"H. Requires 4 AA and 2 D Batteries.
Symbol Communicator #4040		6 4" x 4"	6 on 6 levels	216	Direct	N/A	\$335.95	Touch one of the six removable tactile symbols to activate a message and at the same time you will feel a vibration, which can be turned off if not desired. Tactile symbols are a graphic language system using concrete or abstract representations that are both permanent and manipulatable and can be tactually discriminated by an individual who is totally blind or dual sensory impaired. Size: 14"L x 10½"W x 2"H. Requires 4 AA Batteries.

DEVICE	PHOTO	MESSAGE CELLS CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
Visually Impaired Communicators Small #2040, Large 2041 & Medium 2042		8 to 10 2" x 2"	#2040 & 2041 8 on 6 levels #2042 10 on 6 levels	#2040 & 2041 288 seconds #2042 300 seconds	Direct	N/A	\$345.95- \$395.95 & \$395.95	These units have two dimmable fluorescent tubes which provide intensive background illumination. The icon holders are transparent which allow the therapist/teacher to use clear or transparent icons. (Small) Size: Wedge 15" x 9¼" x 5¼", (Medium) Size: Wedge 18" x 10" x 5", (Large) Size: Wedge 20" x 12" x 7". Requires AC adapter (included) and 4 AA Batteries.
Adjustable Angle Sequencer #806		1 5"	Unlimited within total time	300	Direct	Device Output	\$170.95	Our new sequencer is designed for the visually impaired. The circular patterned red LED lights in the center give the user a visual cue for targeting and encourage the user to activate the switch. The angle of the big 5" switch is adjustable from 32 degrees to 90 degrees. Size: 8"L x 8"W x 6¼"H. Requires 4 AA Batteries.
Illuminated Picture Frame Communicator #1255		4 4" x 5"	4 on 12 levels	300	Direct & Switch	Input Switch	\$340.95	Our new brightly illuminated communicator was designed for those with visual impairments. Push on any of the 4 pictures to activate your pre-recorded message, and illuminate the photo. •Holds up to 8 photographs using front and back •Work in fields of one, two, three, or four •Direct select, single switch scanning, or auditory cueing •Adjustable scan speed of 2, 6, 9 seconds. Size: 12½"D x 19"W x 6"H. Requires 4 D Batteries.
Talking Alert & Talking Alert & Levels #1412 & 1412-L		1 5"	#1412 - 1 #1412-L - 12	20 288	Direct	N/A	\$114.95- \$126.95	Pressing the textured lens turns on a bright light and starts your message. While the message is playing, a circle of lights indicate that words are being played. A special switch on the side of the unit selects levels. Size: 7¾"W x 2½"H. Requires 4 AA Batteries.
Totally Tactile Communicator #2046		6 4½"	6 on 6 levels	252	Direct	N/A	\$249.95	Our tactile communicator is a wonderful place for the VI user to start communication. Around the outside are six plates with different large textures where you record and play back your messages. A large textured level changer is positioned in its center. It is mounted on a Lazy Susan so you can slowly turn the communicator to feel all of your choices before activating a message. Size: 14½"L x 14½"W x 3"H. Requires 4 AA Batteries.

Miscellaneous Devices

DEVICE	PHOTO	MESSAGE CELLS — CELL SIZE	NUMBER OF MESSAGES	TOTAL TIME (SEC)	ACCESS	PORTS	PRICE	FEATURES
<p>NEW! Phonics Fun Communicator #3059</p>		<p style="text-align: center;">4 — 2" x 2"</p>	<p style="text-align: center;">18 levels</p>	<p style="text-align: center;">300</p>	<p style="text-align: center;">Direct</p>	<p style="text-align: center;">N/A</p>	<p style="text-align: center;">\$239.95</p>	<p>A simple and interactive way to teach reading and speaking. Program each of the first three squares with the phonetic sound of a letter and then the name of that letter. Use the last square to record the complete word. For example, to teach the word CAT, program square one with "kuh" then "C"; square two with "ah" then "A", square three with "tuh" then "T"; and square four with "CAT". For reinforcement, the device can be reset to play each phonetic sound from 1 to 4 times. Size: 17"L x 5½"W x 2½"H. Requires 4 AA Batteries.</p>